

Ordering Specifications - Sump Accessories

| Part # | Application |
|--|---|
| SL-1100 | Urethane Sealant |
| S-CS-SEALANT | 2 Part Self Leveling Sealant - Used to Seal Gap Between the Top-Hat and Skirt |
| S-CR-FGK | Kit for Bonding Collar Ring to Tank Collar - Includes Resin, Catalyst and Glass Tape. |
| RK-5000 | Epoxy Resin Kit Bonding Collar Ring Sump to Fiberglass Tank Collar |
| PLEX-TUBE | 1 Tube Of Plexus Adhesive |
| PlexisApplicator | Single Barrel Manual Applicator |
| Contact OPW for Tank Fittings and Manway Adaptors - 1-800-422-2525 | |

Ordering Specifications - Sump Accessories

| Part # | Application |
|---------------|---|
| WSP-WTS-OPC | 6" Nitrile Observation Port Cap for WSP |
| WTS-CAP-14 | 14" Nitrile Container Port Cap for WSP |
| WS-RING-31 | 31" Stainless Steel Retaining Ring for Top-Hat |
| WS-RING-33 | 33" Stainless Steel Retaining Ring for Top-Hat |
| WS-RING-37 | 37" Stainless Steel Retaining Ring for Top-Hat |
| S-TH-RISER-31 | 10" Deep Top-Hat Riser for All 31" Dia. Opening |
| S-TH-RISER-33 | 10" Deep Top-Hat Riser for All 33" Dia. Opening |
| S-TH-RISER-37 | 10" Deep Top-Hat Riser for All 37" Dia. Opening |



New Latched Fiberglass Tank Sump Lids

Our new specially designed latched Fiberglass Tank Sump Lid is now available on our Fiberglass Sump Models. Our new lid can also be ordered as a replacement Lid for our Polyethylene Sumps.

This lid is available to replace the "Mechanically Fastened" lids with knobs on retrofit applications.

Features & Benefits:

- ◆ Six latch and cover design to ensure even sealing.
- ◆ Holes in the lid to allow installation on 33" Fiberglass or Polyethylene Tank Sumps.
- ◆ Lid strength is three times stronger than our previous lid.
- ◆ Retrofitable to existing OPW Polyethylene and Fiberglass Tank Sumps that have the Mechanically Fastened Lid.

Ordering Specifications - New Latched Fiberglass Tank Sump Lids

| Part # | Description |
|---------|--------------------------------------|
| CLC-33 | Latched Fiberglass Tank Sump Lid |
| LRK-CLC | Latch Replacement Kit for the CLC-33 |